



DET NORSKE VERITAS

TYPE APPROVAL CERTIFICATE

CERTIFICATE NO. E-7157

This Certificate consists of 5 pages

This is to certify that the
Enclosure for Electrical Equipment
with type designation(s)
Spacial 6000


Manufactured by
Sarel S.A.
Sarre-Union Cedex, France

is found to comply with
Det Norske Veritas' Rules for Classification of Ships, High Speed & Light Craft and Det Norske Veritas' Offshore Standards

Application


Enclosure protection	IP 55
Vibration class	A

Place and date
Høvik, 2004-11-24
for DET NORSKE VERITAS AS


Gro Elisabeth Paulsrud
Head of Section


Local Office
DNV Marseille

This Certificate is valid until
2008-12-31


Nicolay Horn
Surveyor

Notice: This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

If any person suffers loss or damage which is proved to have been caused by any negligent act or omission of Det Norske Veritas, then Det Norske Veritas shall pay compensation to such person for his proved direct loss or damage. However, the compensation shall not exceed an amount equal to ten times the fee charged for the service in question, provided that the maximum compensation shall never exceed USD 2 million. In this provision "Det Norske Veritas" shall mean the Foundation Det Norske Veritas as well as all its subsidiaries, directors, officers, employees, agents and any other acting on behalf of Det Norske Veritas.



Cert. No.: E-7157
File No.: 829.20

Product description

Spacial 6000 front door/ rear panel, with or without plain chassis

External dimensions			front doors	with plain front door	with plain front door + plain chassis	with altuglas glazed front door
H	W	D	no	ref. no	ref. no	ref. no
mm	mm	mm				
1600	600	600	1	61240	67540	-
1600	600	800	1	61241	67541	-
1600	800	600	1	61242	67542	-
1600	800	800	1	61243	67543	-
1800	300	600	1	61250	-	-
1800	300	800	1	61251	-	-
1800	600	400	1	61264	67564	61564
1800	600	500	1	61265	67565	64565
1800	600	600	1	61266	67566	61566
1800	600	800	1	61268	67568	61568
1800	800	400	1	61274	67574	61574
1800	800	500	1	61275	67575	61575
1800	800	600	1	61276	67576	61576
1800	800	600	1	61277	67577	61577
1800	1000	400	2	61279	67579	61579
1800	1000	400	1	61479	67779	61779
1800	1000	600	2	61281	67581	61581
1800	1000	600	1	61481	67781	61781
1800	1200	400	2	61284	67584	61584
1800	1200	500	2	61285	67585	61585
1800	1200	600	2	61286	67586	61586
2000	300	400	2	61313	-	-
2000	300	500	2	61340	-	-
2000	300	600	2	61341	-	-
2000	400	500	1	61345	-	-
2000	400	600	1	61346	-	-
2000	600	400	1	61314	67614	61614
2000	600	500	1	61315	67615	61615

External dimensions			front doors	with plain front door	with plain front door + plain chassis	with altuglas glazed front door
H	W	D	no	ref. no	ref. no	ref. no
mm	mm	mm				
2000	600	600	1	61316	67616	61616
2000	600	800	1	61318	67618	61618
2000	800	400	1	61324	67624	61624
2000	800	500	1	61325	67625	61625
2000	800	600	1	61326	67626	61626
2000	800	800	1	61327	67627	61627
2000	800	800	1	61328	67628	61628
2000	1000	400	2	61329	67629	61629
2000	1000	400	1	61529	67829	61829
2000	1000	500	2	61330	67630	61630
2000	1000	500	1	61530	67830	61830
2000	1000	600	2	61331	67631	61631
2000	1000	600	1	61531	67831	61831
2000	1000	800	2	61333	67633	61633
2000	1000	800	1	61533	67833	61833
2000	1200	400	2	61334	67634	61634
2000	1200	500	2	61335	67635	61635
2000	1200	600	2	61336	67636	61636
2000	1200	800	2	61338	67638	61638
2000	1200	800	2	61339	67639	61639
2200	600	600	1	61366	67666	61666
2200	600	800	1	61368	67668	61668
2200	800	600	1	61376	67676	61676
2200	800	800	1	61378	67678	61678
2200	1200	600	2	61386	67686	61686
2200	1200	800	2	61388	67688	61688



Cert. No.: E-7157

File No.: 829.20

Spacial 6000 front door/ rear door

External dimensions			front doors	rear doors	with plain front door	with altuglas glazed front door
H	W	D	no	no	ref. no	ref. no
mm	mm	mm				
1200	600	600	1	1	60206	-
1200	600	800	1	1	60208	-
1200	800	600	1	1	60216	-
1200	800	800	1	1	60218	-
1600	600	600	1	1	60236	-
1600	600	800	1	1	60238	-
1600	800	600	1	1	60246	-
1600	800	800	1	1	60248	-
1800	600	400	1	1	60264	60564
1800	600	500	1	1	60265	60565
1800	600	600	1	1	60266	60566
1800	600	800	1	1	60268	60568
1800	800	400	1	1	60274	60574
1800	800	500	1	1	60275	60575
1800	800	600	1	1	60276	60576
1800	1000	400	1	2	60279	60579
1800	1000	600	1	2	60281	60581
1800	1200	400	2	2	60284	60584
1800	1200	500	2	2	60285	60585
1800	1200	600	2	2	60286	60586
2000	600	400	1	1	60314	60614
2000	600	500	1	1	60315	60615

External dimensions			front doors	rear doors	with plain front door	with altuglas glazed front door
H	W	D	no	no	ref. no	ref. no
mm	mm	mm				
2000	600	600	1	1	60316	60616
2000	600	800	1	1	60318	60618
2000	800	400	1	1	60324	60624
2000	800	500	1	1	60325	60625
2000	800	600	1	1	60326	60626
2000	800	800	1	1	60328	60628
2000	1000	400	1	2	60329	60629
2000	1000	500	1	2	60330	60630
2000	1000	600	1	2	60331	60631
2000	1000	800	1	2	60333	60633
2000	1200	400	2	2	60334	60634
2000	1200	500	2	2	60335	60635
2000	1200	600	2	2	60336	60636
2000	1200	800	2	2	60338	60638
2200	600	600	1	1	60366	60666
2200	600	800	1	1	60368	60668
2200	800	600	1	1	60376	60676
2200	800	800	1	1	60378	60678
2200	1200	600	2	2	60386	60686
2200	1200	800	2	2	60388	60688

Spacial 6000 19" rack

External dimensions			front door	rear door	with transparent door RAL 7011	with transparent door RAL 7032	with trim frame RAL 7011
H	W	D	no	no	ref. no	ref. no	ref. no
mm	mm	mm					
1200	600	600	1	1	67906	68206	68406
1200	600	800	1	1	67908	68208	68408
1200	800	600	1	1	67916	68216	-
1200	800	800	1	1	67918	68218	-
1600	600	600	1	1	67936	68236	68426

External dimensions			front door	rear door	with transparent door RAL 7011	with transparent door RAL 7032	with trim frame RAL 7011
H	W	D	no	no	ref. no	ref. no	ref. no
mm	mm	mm					
1600	600	800	1	1	67938	68238	68428
1600	800	600	1	1	67946	68246	-
1600	800	800	1	1	67948	68248	-
1800	600	600	1	1	67956	68256	68436
1800	600	800	1	1	67958	68258	68438



Cert. No.: E-7157

File No.: 829.20

External dimensions			front door	rear door	with transparent door RAL 7011	with transparent door RAL 7032	with trim frame RAL 7011
H	W	D	no	no	ref. no	ref. no	ref. no
mm	mm	mm					
1800	800	600	1	1	67966	68266	-
1800	800	800	1	1	67968	68268	-
2000	600	600	1	1	67976	68276	68466
2000	600	800	1	2	67978	68278	68468
2000	800	600	1	2	67986	68286	-

External dimensions			front door	rear door	with transparent door RAL 7011	with transparent door RAL 7032	with trim frame RAL 7011
H	W	D	no	no	ref. no	ref. no	ref. no
mm	mm	mm					
2000	800	800	2	2	67988	68288	-
2200	600	600	2	2	67996	68296	68486
2200	600	800	2	2	67998	68298	68488
2200	800	600	1	1	68106	68306	-
2200	800	800	1	1	68108	68308	-

Compartmentalised

External dimensions			Usable High doors	Compart. Encl. reference	Set of 2 side panels
H	W	D	mm	ref. no	ref. no
mm	mm	mm	mm		
1800	600	600	1600	65500	61036
1800	600	800	1600	65501	61038
1800	800	600	1600	65502	61036
1800	800	800	1600	65503	61038
1800	1000	600	1600	65504	61036
1800	1000	800	1600	65505	61038
1800	1200	600	1600	65506	61036
1800	1200	800	1600	65507	61038

External dimensions			Usable High doors	Compart. Encl. reference	Set of 2 side panels
H	W	D	mm	ref. no	ref. no
mm	mm	mm	mm		
2000	600	600	1800	65510	61046
2000	600	800	1800	65511	61048
2000	800	600	1800	65512	61046
2000	800	800	1800	65513	61048
2000	1000	600	1800	65514	61046
2000	1000	800	1800	65515	61048
2000	1200	600	1800	65516	61046
2000	1200	800	1800	65517	61048

Type Approval documentation

Brochure: SAREL Catalogue 2001 edition 8 (partly), SAREL Spacial 6000 no. 9509025 - 1 - 2500:N/S/NL/Exp.r.t

Test reports: SP 94F21071 dated 94-09-09.

Tests carried out

Vibration test.

Marking of product

SAREL S.A. - Type designation - Reference number



Cert. No.: E-7157

File No.: 829.20

Certificate retention survey

The scope of the retention/renewal survey is to verify that the conditions stipulated for the type approval is complied with and that no alterations are made to the product design or choice of materials.

The main elements of the survey to be dealt with:

- Ensure that type approved documentation is available.
- Ensure that materials used comply with type approved documents and/or referenced material specifications.
- Review design, materials, performance and production process with respect to possible changes, in order to ensure compliance with the type approved documentation and/or referenced material specifications.
- Ensure traceability between manufacturer's product marking and the DNV Type Approval Certificate.

Survey to be performed only by renewal.

END OF CERTIFICATE

LISTE DES REFERENCES CONCERNEES PAR LE PRESENT CERTIFICAT
LIST OF REFERENCES CONCERNED BY THIS CERTIFICATE

REFERENCE	DESIGNATION
60206	Cellule 1pte arr.1200x600x600
60208	Cellule 1pte arr.1200x600x800
60216	Cellule 1pte arr.1200x800x600
60218	Cellule 1pte arr.1200x800x800
60236	Cellule 1pte arr.1600x600x600
60238	Cellule 1pte arr.1600x600x800
60246	Cellule 1pte arr.1600x800x600
60248	Cellule 1pte arr.1600x800x800
60264	Cellule 1pte arr.1800x600x400
60265	Cellule 1pte arr.1800x600x500
60266	Cellule 1pte arr.1800x600x600
60268	Cellule 1pte arr.1800x600x800
60274	Cellule 1pte arr.1800x800x400
60275	Cellule 1pte arr.1800x800x500
60276	Cellule 1pte arr.1800x800x600
60279	Cellule 2ptes arr1800x1000x400
60281	Cellule 2ptes arr1800x1000x600
60284	Cellule 2ptes arr1800x1200x400
60285	Cellule 2ptes arr1800x1200x500
60286	Cellule 2ptes arr1800x1200x600
60314	Cellule 1pte arr.2000x600x500
60315	Cellule 1pte arr.2000x600x600
60316	Cellule 1pte arr.2000x600x600
60318	Cellule 1pte arr.2000x600x800
60324	Cellule 1pte arr.2000x800x400
60325	Cellule 1pte arr.2000x800x500
60326	Cellule 1pte arr.2000x800x600
60328	Cellule 1pte arr.2000x800x800
60329	Cellule 2ptes arr2000x1000x400
60330	Cellule 2ptes arr2000x1000x500
60331	Cellule 2ptes arr2000x1000x600
60333	Cellule 2ptes arr2000x1000x800
60334	Cellule 2ptes arr2000x1200x400
60335	Cellule 2ptes arr2000x1200x500
60336	Cellule 2ptes arr2000x1200x600
60338	Cellule 2ptes arr2000x1200x800
60366	Cell.1 pte arr. 2200x600x600
60368	Cell.1 pte arr. 2200x600x800
60376	Cell.1 pte arr. 2200x800x600
60378	Cell.1 pte arr. 2200x800x800
60386	Cell.2 ptes arr.2200x1200x600
60388	Cell.2 ptes arr.2200x1200x800
60564	Cell.tr 1 pte ar.1800x600x400
60565	Cell.tr 1 pte ar.1800x600x500
60566	Cell.tr 1 pte ar.1800x600x600

REFERENCE	DESIGNATION
61628	Cell.tr a/pan ar. 2000x800x800
61629	Cell.tr a/pan ar.2000x1000x400
61630	Cell.tr a/pan ar.2000x1000x500
61631	Cell.tr a/pan ar.2000x1000x600
61633	Cell.tr a/pan ar.2000x1000x800
61634	Cell.tr a/pan ar.2000x1200x400
61635	Cell.tr a/pan ar.2000x1200x500
61636	Cell.tr a/pan ar.2000x1200x600
61638	Cell.tr a/pan ar.2000x1200x800
61666	Cell.tr a/pan ar.2200x600x600
61668	Cell.tr a/pan ar.2200x600x800
61676	Cell.tr a/pan ar.2200x800x600
61678	Cell.tr a/pan ar.2200x800x800
61686	Cell.tr a/pan ar.2200x1200x600
61688	Cell.tr a/pan ar.2200x1200x800
61779	Cell.tr a/pan ar.1800x1000x400
61781	Cell.tr a/pan ar.1800x1000x600
61829	Cell.tr a/pan ar.2000x1000x400
61830	Cell.tr a/pan ar.2000x1000x500
61831	Cell.tr a/pan ar.2000x1000x600
61833	Cell.tr a/pan ar.2000x1000x800
67540	Cell.av.chassis 1600x600x600
67541	Cell.av.chassis 1600x600x800
67542	Cell.av.chassis 1600x800x600
67543	Cell.av.chassis 1600x800x800
67564	Cell.a/cha.pl.1p.1800x600x400
67565	Cell.a/cha.pl.1p.1800x600x500
67566	Cell.a/cha.pl.1p.1800x600x600
67568	Cell.a/cha.pl.1p.1800x600x800
67574	Cell.a/cha.pl.1p.1800x800x400
67575	Cell.a/cha.pl.1p.1800x800x500
67576	Cell.a/cha.pl.1p.1800x800x600
67577	Cell.a/cha.pl.2p.1800x800x600
67579	Cell.a/cha.pl.2p.1800x1000x400
67581	Cell.a/cha.pl.2p.1800x1000x600
67584	Cell.a/cha.pl.2p.1800x1200x400
67585	Cell.a/cha.pl.2p.1800x1200x500
67586	Cell.a/cha.pl.2p.1800x1200x600
67614	Cell.a/cha.pl.1p.2000x600x400
67615	Cell.a/cha.pl.1p.2000x600x500
67616	Cell.a/cha.pl.1p.2000x600x600
67618	Cell.a/cha.pl.1p.2000x600x800
67624	Cell.a/cha.pl.1p.2000x800x400
67625	Cell.a/cha.pl.1p.2000x800x500
67626	Cell.a/cha.pl.1p.2000x800x600

60568	Cell.tr 1 pte ar.1800x600x800
60574	Cell.tr 1 pte ar.1800x800x400
60575	Cell.tr 1 pte ar.1800x800x500
60576	Cell.tr 1 pte ar.1800x800x600
60579	Cell.tr 2 p. ar.1800x1000x400
60581	Cell.tr 2 p. ar.1800x1000x600
60584	Cell.tr 2 p. ar.1800x1200x400
60585	Cell.tr 2 p. ar.1800x1200x500
60586	Cell.tr 2 p. ar.1800x1200x600
60614	Cell.tr 1 pte ar.2000x600x400
60615	Cell.tr 1 pte ar.2000x600x500
60616	Cell.tr 1 pte ar.2000x600x600
60618	Cell.tr 1 pte ar.2000x600x800
60624	Cell.tr 1 pte ar.2000x800x400
60625	Cell.tr 1 pte ar.2000x800x500
60626	Cell.tr 1 pte ar.2000x800x600
60628	Cell.tr 1 pte ar.2000x800x800
60629	Cell.tr 2 p. ar.2000x1000x400
60630	Cell.tr 2 p. ar.2000x1000x500
60631	Cell.tr 2 p. ar.2000x1000x600
60633	Cell.tr 2 p. ar.2000x1000x800
60634	Cell.tr 2 p. ar.2000x1200x400
60635	Cell.tr 2 p. ar.2000x1200x500
60636	Cell.tr 2 p. ar.2000x1200x600
60638	Cell.tr 2 p. ar.2000x1200x800
60666	Cell.tr 1 pte ar.2200x600x600
60668	Cell.tr 1 pte ar.2200x600x800
60676	Cell.tr 1 pte ar.2200x800x600
60678	Cell.tr 1 pte ar.2200x800x800
60686	Cell.tr 2 p. ar.2200x1200x600
60688	Cell.tr 2 p. ar.2200x1200x800
61240	Cell.a/pan. arr.1600x600x600
61241	Cell.a/pan. arr.1600x600x800
61242	Cell.a/pan. arr.1600x800x600
61243	Cell.a/pan. arr.1600x800x800
61250	Cell.a/pan. arr.1800x300x500
61251	Cell.a/pan. arr.1800x300x600
61264	Cell.a/pan. arr. 1800x600x400
61265	Cell.a/pan. arr. 1800x600x500
61266	Cell.a/pan. arr. 1800x600x600
61268	Cell.a/pan. arr. 1800x600x800
61274	Cell.a/pan. arr. 1800x800x400
61275	Cell.a/pan. arr. 1800x800x500
61276	Cell.a/pan. arr. 1800x800x600
61277	Cell.2p+1 pan.arr.1800x800x600
61279	Cell.a/pan. arr. 1800x1000x400
61281	Cell.a/pan. arr. 1800x1000x600
61284	Cell.a/pan. arr. 1800x1200x400
61285	Cell.a/pan. arr. 1800x1200x500
61286	Cell.a/pan. arr. 1800x1200x600
61313	Cell.a/pan. Arr. 2000x300x400
61314	Cell.a/pan. arr. 2000x600x400
61315	Cell.a/pan. arr. 2000x600x500

67627	Cell.a/cha.pl.2p.2000x800x600
67628	Cell.a/cha.pl.1p.2000x800x800
67629	Cell.a/cha.pl.2p.2000x1000x400
67630	Cell.a/cha.pl.2p.2000x1000x500
67631	Cell.a/cha.pl.2p.2000x1000x600
67633	Cell.a/cha.pl.2p.2000x1000x800
67634	Cell.a/cha.pl.2p.2000x1200x400
67635	Cell.a/cha.pl.2p.2000x1200x500
67636	Cell.a/cha.pl.2p.2000x1200x600
67638	Cell.a/cha.pl.2p.2000x1200x800
67639	Cell.a/cha.pl.2p.2000x1600x400
67666	Cell.a/cha.pl.1p.2200x600x600
67668	Cell.a/cha.pl.1p.2200x600x800
67676	Cell a/cha.pl.1p.2200x800x600
67678	Cell.a/cha.pl.1p.2200x800x800
67686	Cell.a/cha.pl.2p.2200x1200x600
67688	Cell.a/cha.pl.2p.2200x1200x800
67779	Cell.a/cha.pl.1p.1800x1000x400
67781	Cell.a/cha.pl.1p.1800x1000x600
67829	Cell.a/cha.pl.1p.2000x1000x400
67830	Cell.a/cha.pl.1p.2000x1000x500
67831	Cell.a/cha.pl.1p.2000x1000x600
67833	Cell.a/cha.pl.1p.2000x1000x800
67906	Baie pte tr.R7011 1200x600x600
67908	Baie pte tr.R7011 1200x600x800
67916	Baie pte tr.R7011 1200x800x600
67918	Baie pte tr.R7011 1200x800x800
67936	Baie pte tr.R7011 1600x600x600
67938	Baie pte tr.R7011 1600x600x800
67946	Baie pte tr.R7011 1600x800x600
67948	Baie pte tr.R7011 1600x800x800
68206	Baie pte tr.R7032 1200x600x600
68208	Baie pte tr.R7032 1200x600x800
68216	Baie pte tr.R7032 1200x800x600
68218	Baie pte tr.R7032 1200x800x800
68236	Baie pte tr.R7032 1600x600x600
68238	Baie pte tr.R7032 1600x600x800
68246	Baie pte tr.R7032 1600x800x600
68248	Baie pte tr.R7032 1600x800x800
68406	Baie 6000 a/enjo.1200x600x600
68408	Baie 6000 a/enjo.1200x600x800
68426	Baie 6000 a/enjo.1600x600x600
68428	Baie 6000 a/enjo.1600x600x800
67956	Baie pte tr.R7011 1800x600x600
67958	Baie pte tr.R7011 1800x600x800
67966	Baie pte tr.R7011 1800x800x600
67968	Baie pte tr.R7011 1800x800x800
67976	Baie pte tr.R7011 2000x600x600
67978	Baie pte tr.R7011 2000x600x800
67986	Baie pte tr.R7011 2000x800x600
67988	Baie pte tr.R7011 2200x800x800
67996	Baie pte tr.R7011 2200x600x600
67998	Baie pte tr.R7011 2200x600x800

61316	Cell.a/pan. arr. 2000x600x600
61318	Cell.a/pan. arr. 2000x600x800
61324	Cell.a/pan. arr. 2000x800x400
61325	Cell.a/pan. arr. 2000x800x500
61326	Cell.a/pan. arr. 2000x800x600
61327	Cell.2p+2 pan.arr.2000x800x600
61328	Cell.a/pan. arr. 2000x800x800
61329	Cell.a/pan. arr. 2000x1000x400
61330	Cell.a/pan. arr. 2000x1000x500
61331	Cell.a/pan. arr. 2000x1000x600
61333	Cell.a/pan. arr. 2000x1000x800
61334	Cell.a/pan. arr. 2000x1200x400
61335	Cell.a/pan. arr. 2000x1200x500
61336	Cell.a/pan. arr. 2000x1200x600
61338	Cell.a/pan. arr. 2000x1200x800
61339	Cell.a/pan. arr. 2000x1600x400
61340	Cell.a/pan. arr. 2000x300x500
61341	Cell.a/pan. arr. 2000x300x600
61345	Cell.a/pan. arr. 2000x400x500
61346	Cell.a/pan. arr. 2000x400x600
61366	Cell.a/pan. arr. 2200x600x600
61368	Cell.a/pan. arr. 2200x600x800
61376	Cell.a/pan. arr. 2200x800x600
61378	Cell.a/pan. arr. 2200x800x800
61386	Cell.a/pan. arr. 2200x1200x600
61388	Cell.a/pan. arr. 2200x1200x800
61479	Cell.a/pan. arr. 1800x1000x400
61481	Cell.a/pan. arr. 1800x1000x600
61529	Cell.a/pan. arr. 2000x1000x400
61530	Cell.a/pan. arr. 2000x1000x500
61531	Cell.a/pan. arr. 2000x1000x600
61533	Cell.a/pan. arr. 2000x1000x800
61564	Cell.tr a/pan ar. 1800x600x400
61565	Cell.tr a/pan ar. 1800x600x500
61566	Cell.tr a/pan ar. 1800x600x600
61568	Cell.tr a/pan ar. 1800x600x800
61574	Cell.tr a/pan ar. 1800x800x400
61575	Cell.tr a/pan ar. 1800x800x500
61576	Cell.tr a/pan ar. 1800x800x600
61579	Cell.tr a/pan ar.1800x1000x400
61581	Cell.tr a/pan ar.1800x1000x600
61584	Cell.tr a/pan ar.1800x1200x400
61585	Cell.tr a/pan ar.1800x1200x500
61586	Cell.tr a/pan ar.1800x1200x600
61614	Cell.tr a/pan ar. 2000x600x400
61615	Cell.tr a/pan ar. 2000x600x500
61616	Cell.tr a/pan ar. 2000x600x600
61618	Cell.tr a/pan ar. 2000x600x800
61624	Cell.tr a/pan ar. 2000x800x400
61625	Cell.tr a/pan ar. 2000x800x500
61626	Cell.tr a/pan ar. 2000x800x600

68106	Baie pte tr.R7011 2200x800x600
68108	Baie pte tr.R7011 2200x800x800
68256	Baie pte tr.R7032 1800x600x600
68258	Baie pte tr.R7032 1800x600x800
68266	Baie pte tr.R7032 1800x800x600
68268	Baie pte tr.R7032 1800x800x800
68276	Baie pte tr.R7032 2000x600x600
68278	Baie pte tr.R7032 2000x600x800
68286	Baie pte tr.R7032 2000x800x600
68288	Baie pte tr.R7032 2200x800x800
68296	Baie pte tr.R7032 2200x600x600
68298	Baie pte tr.R7032 2200x600x800
68306	Baie pte tr.R7032 2200x800x600
68308	Baie pte tr.R7032 2200x800x800
68436	Baie 6000 a/enjo.1800x600x600
68438	Baie 6000 a/enjo.1800x600x800
68466	Baie 6000 a/enjo.2000x600x600
68468	Baie 6000 a/enjo.2000x600x800
68486	Baie 6000 a/enjo.2200x600x600
68488	Baie 6000 a/enjo.2200x600x800
65500	Cellule vide mont.1800x600x600
65501	Cellule vide mont.1800x600x800
65502	Cellule vide mont.1800x800x600
65503	Cellule vide mont.1800x800x800
65504	Cell+pann.abatt.1800x1000x600
65505	Cell+pann.abatt.1800x1000x800
65506	Cell+pann.abatt.1800x1200x600
65507	Cell+pann.abatt.1800x1200x800
65510	Cellule vide mont.2000x600x600
65511	Cellule vide mont.2000x600x800
65512	Cellule vide mont.2000x800x600
65513	Cellule vide mont.2000x800x800
65514	Cell+pann.abatt.2000x1000x600
65515	Cell+pann.abatt.2000x1000x800
65516	Cell+pann.abatt.2000x1200x600
65517	Cell+pann.abatt.2000x1200x800